



SFT240

2-pole, 40A Centre Off Modular Changeover Switch with Top Common Point

Technical characteristics

Architecture

Number of poles	2 P
Type of pole	2 P

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power

Total power loss under I _N	4.2 W
---------------------------------------	-------

Endurance

Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------