



SK602



Voltmeter switch 3"o

Technical characteristics

Main electrical features

Rated operational voltage U_e	660 V
Frequency	50 Hz

Voltage

Rated insulation voltage	690 V
--------------------------	-------

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Total power loss under IN	1 W
---------------------------	-----

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1,5 / 10mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Type of connection	with screw

Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------