




SK606



## Switch with key 10A

### Technical characteristics

#### Architecture

Number of poles	2 P
-----------------	-----

#### Controls and indicators

Indicator lamp	no
----------------	----

#### Main electrical features

Rated operational voltage $U_e$	400 V
---------------------------------	-------

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	440 V
--------------------------	-------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

#### Power

Total power loss under IN	1 W
---------------------------	-----

#### Connection

Connection cross-sect. flexible conductor	1,5 / 10mm <sup>2</sup>
---	-------------------------

Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
------------------------------------	----------------------

Type of connection	with screw
--------------------	------------

Number of contacts	2
--------------------	---

Type of contacts	1NO
------------------	-----

#### Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------