




SK606



**Switch with key 20A**

**Technical characteristics**

**Architecture**

Number of poles	2 P
-----------------	-----

**Controls and indicators**

Indicator lamp	no
----------------	----

**Main electrical features**

Rated operational voltage Ue	400 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	440 V
--------------------------	-------

**Dimensions**

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	70 mm

**Power**

Total power loss under IN	1 W
---------------------------	-----

**Connection**

Number of contacts	2
Type of contacts	1NO

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-10...40 °C
-----------------------	-------------