




SK606



## Switch with key 20A

### Technical characteristics

#### Architecture

Number of poles 2 P

#### Controls and indicators

Indicator lamp no

#### Main electrical features

Rated operational voltage  $U_e$  400 V

Frequency 50 Hz

#### Voltage

Rated insulation voltage 440 V

#### Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 70 mm

#### Power

Total power loss under IN 1 W

#### Connection

Number of contacts 2

Type of contacts 1NO

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...40 °C