




SK606



Switch with key 20A

Technical characteristics

Architecture

Number of poles	2 P
-----------------	-----

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Rated operational voltage U _e	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	440 V
--------------------------	-------

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Total power loss under I _N	1 W
---------------------------------------	-----

Connection

Connection cross-sect. flexible conductor	1,5 / 10mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Number of contacts	2
Type of contacts	1NO

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------