



SM100

### Analogue ammeter 0-100A indirect reading

#### Technical characteristics

#### Main electrical features

Frequency	45/65 Hz
-----------	----------

#### Voltage

Rated insulation voltage	2000 V
--------------------------	--------

#### Dimensions

Depth of installed product	54 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

#### Power

Power consumed	1.1 VA
----------------	--------

Total power loss under IN	1.1 W
---------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
------------------------------------	-------------------------

#### Use conditions

Operating temperature	-25...50 °C
-----------------------	-------------