



SM100

**Analogue ammeter 0-100A indirect reading**

**Technical characteristics**

**Architecture**

Fixing mode	Din-Rail
-------------	----------

**Voltage**

Rated insulation voltage	2000 V
--------------------------	--------

**Dimensions**

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

**Power**

Power consumed	1.1 VA
Total power loss under IN	1.1 W

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-25...50 °C
-----------------------	-------------