



SM101C

Communicant Modular multifunction meter

Technical characteristics

Main electrical features

Rated operational voltage U_e 200 / 230 / 277 V

Frequency 50/60 Hz

Dimensions

Depth of installed product 50 mm

Height of installed product 45 mm

Width of installed product 73 mm

Power

Power consumed 5 VA

Total power loss under IN 5 W

Measurement

Type of measuring instrument multimeter

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 0,5 / 4mm²

Connection cross-sect. rigid cable 0,5 / 4mm²

Type of connection with screw

Equipment

Type of display Digital

Use conditions

Operating temperature -10...55 °C