



SM101E

Modular multifunction meter

Technical characteristics

Main electrical features

Rated operational voltage Ue	200 / 230 / 277 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	50 mm
Height of installed product	45 mm
Width of installed product	73 mm

Power

Power consumed	5 VA
Total power loss under IN	5 W

Measurement

Type of measuring instrument	multimeter
------------------------------	------------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	0,5 / 4mm ²
Connection cross-sect. rigid cable	0,5 / 4mm ²
Type of connection	with screw

Equipment

Type of display	Digital
-----------------	---------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------