



SM150

Analogue ammeter 0-150A indirect reading

Technical characteristics

Voltage

| | |
|--------------------------|--------|
| Rated insulation voltage | 2000 V |
|--------------------------|--------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 54 mm |
| Height of installed product | 85 mm |
| Width of installed product | 70 mm |

Power

| | |
|---------------------------|--------|
| Power consumed | 1.1 VA |
| Total power loss under IN | 1.1 W |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25...50 °C |
|-----------------------|-------------|