



SM151

### Digital ammeter 0-150A indirect reading

#### Technical characteristics

##### Main electrical features

Rated operational voltage  $U_e$  207 / 230 / 253 V

Frequency 45/65 Hz

##### Dimensions

Depth of installed product 54 mm

Height of installed product 85 mm

Width of installed product 70 mm

##### Power

Power consumed 1 VA

Total power loss under IN 1 W

##### Connection

Connection cross-sect. flexible conductor 6mm<sup>2</sup>

Connection cross-sect. rigid cable 10mm<sup>2</sup>

##### Use conditions

Operating temperature -10...55 °C