



SM151

### Digital ammeter 0-150A indirect reading

#### Technical characteristics

##### Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
Frequency	45/65 Hz

##### Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

##### Power

Power consumed	1 VA
Total power loss under IN	1 W

##### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>

##### Safety

Protection index IP	IP20
---------------------	------

##### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------