



SM401

Digital ammeter 0-400A indirect reading

Technical characteristics

Main electrical features

Rated operational voltage U_e	207 / 230 / 253 V
Frequency	45/65 Hz

Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Power consumed	1 VA
Total power loss under IN	1 W

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	6mm ²
Connection cross-sect. rigid cable	10mm ²

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------