



SM401

## Digital ammeter 0-400A indirect reading

### Technical characteristics

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
------------------------------	-------------------

#### Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

#### Power

Power consumed	1 VA
Total power loss under IN	1 W

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------