



SM500

### Analogie voltmeter 0-500V

#### Technical characteristics

##### Main electrical features

Frequency	45/65 Hz
-----------	----------

##### Voltage

Rated insulation voltage	2000 V
--------------------------	--------

##### Dimensions

Depth of installed product	54 mm
Height of installed product	90 mm
Width of installed product	70 mm

##### Power

Power consumed	3 VA
Total power loss under IN	3.5 W

##### Installation, mounting

Mounting type	din-Rail
---------------	----------

##### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>

##### Safety

Protection index IP	IP20
---------------------	------

##### Use conditions

Operating temperature	-25...50 °C
-----------------------	-------------