



SM500

Analogie voltmeter 0-500V

Technical Characteristics

Fixing mode	Din-Rail
Frequency	45/65 Hz
Rated insulation voltage	2000 V
Depth of installed product	54 mm
Height of installed product	90 mm
Width of installed product	70 mm
Power consumed	3 VA
Total power loss under IN	3.5 W
Type of measuring instrument	voltmeter
Number of modules	4
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Protection index IP	IP20
Operating temperature	-25...50 °C