



SM601

Digital ammeter 0-600A indirect reading

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
------------------------------	-------------------

Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Power consumed	1 VA
Total power loss under IN	1.1 W

Installation, mounting

Mounting type	din-Rail
---------------	----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------