



SM601

### Digital ammeter 0-600A indirect reading

#### Technical characteristics

##### Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
------------------------------	-------------------

##### Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

##### Power

Power consumed	1 VA
Total power loss under IN	1.1 W

##### Safety

Protection index IP	IP20
---------------------	------

##### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------