



SPA080

**Cartridge L-N Uc 264V Iimp 25kA I<sub>max</sub> 50kA Up 1.5kV for SPA180**

**Technical characteristics**

**Controls and indicators**

---

Indicator lamp	Optic
----------------	-------

**Main electrical features**

---

Frequency	50/60 Hz
-----------	----------

**Electric current**

---

Max discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	50 kA
--	-------

**Dimensions**

---

Depth of installed product	52.3 mm
Height of installed product	109.9 mm
Width of installed product	35.5 mm

**Use conditions**

---

Operating temperature	-40...80 °C
-----------------------	-------------