



SPA080

Cartridge L-N Uc 264V Iimp 25kA Imax 50kA Up 1.5kV for SPA180

Technical characteristics

Controls and indicators

| | |
|----------------|-------|
| Indicator lamp | Optic |
|----------------|-------|

Main electrical features

| | |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

Electric current

| | |
|-------------------------------------|-------|
| Max discharge (Imax) L-N(PEN)/ N-PE | 50 kA |
|-------------------------------------|-------|

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 52.3 mm |
| Height of installed product | 109.9 mm |
| Width of installed product | 35.5 mm |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -40...80 °C |
|-----------------------|-------------|