



SPA080

Cartridge L-N Uc 264V Iimp 25kA I_{max} 50kA Up 1.5kV for SPA180

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	50 kA
--	-------

Dimensions

Depth of installed product	52.3 mm
----------------------------	---------

Height of installed product	109.9 mm
-----------------------------	----------

Width of installed product	35.5 mm
----------------------------	---------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------