



SPA090N

Cartridge1P T1+T2 N-PE SPA9xxx

Technical characteristics

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	240 / 415 V
Frequency	50/60 Hz

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	50 kA
--	-------

Dimensions

Depth of installed product	77.5 mm
Height of installed product	47 mm
Width of installed product	17.7 mm

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------