



SPA090N

**Cartridge1P T1+T2 N-PE SPA9xxx**

**Technical characteristics**

**Electric current**

Max. discharge (I<sub>max</sub>) L-N(PEN)/ N-PE 50 kA

**Network configuration**

Network type TN-S, TT

**Connectivity**

Type of connection Plug-in connection

**Equipment**

With remote signalling contact Yes

**Capacity**

Number of modules 1

**Voltage**

Voltage protection level U<sub>p</sub> according to IEC 61643-1 1.70 kV

Continuous operating voltage U<sub>c</sub> according to IEC 61643-1 264 V

**Architecture**

Number of poles 1

**Use conditions**

Operating temperature -40 - 80 °C

**Dimensions**

Height 47.3 mm

Width 17.5 mm

Depth 67.3 mm

**Controls and indicators**

With indicator lamp Yes

**Standards**

Requirement class IEC 61643 T1, T2