



SPA401

SPD 4P monobloc 12.5kA class 1 with light indicator TT + TNS

Technical characteristics

Architecture

Type of pole 4 P

Main electrical features

Rated operational voltage U_e 230 / 400 V

Frequency 50/60 Hz

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 12.5 kA

Power

Total power loss under I_N 0 W

Installation, mounting

Tightening torque 4Nm

Standards

European directive WEEE concerned

Use conditions

Operating temperature -40...80 °C