



SPA401

SPD 4P monobloc 12.5kA class 1 with light indicator TT + TNS

Technical characteristics

Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	12.5 kA
-------------------------------------	---------

Power

Total power loss under IN	0 W
---------------------------	-----

Installation, mounting

Tightening torque	4Nm
-------------------	-----

Connection

Connection cross-sect. flexible conductor	1,5 / 25mm ²
-------------------------------------------	-------------------------

Connection cross-sect. rigid cable	1,5 / 35mm ²
------------------------------------	-------------------------

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------