



SPA401

SPD 4P monobloc 12.5kA class 1 with light indicator TT + TNS

Technical characteristics

Architecture

Type of pole 4 P

Controls and indicators

Indicator lamp end of life indicator

Main electrical features

Rated operational voltage Ue 230 / 400 V

Frequency 50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 12.5 kA

Power

Total power loss under IN 0 W

Installation, mounting

Tightening torque 4Nm

Connection

Connection cross-sect. flexible conductor 1,5 / 25mm²

Connection cross-sect. rigid cable 1,5 / 35mm²

Use conditions

Operating temperature -40...80 °C