



SPA401

SPD 4P monobloc 12.5kA class 1 with light indicator TT + TNS

Technical Characteristics

Type of pole	4 P
Indicator lamp	end of life indicator
Rated operational voltage Ue	230 / 400 V
Frequency	50/60 Hz
Max discharge (Imax) L-N(PEN)/ N-PE	12.5 kA
Total power loss under IN	0 W
Number of modules	4
Tightening torque	4Nm
Connection cross-sect. flexible conductor	1,5 / 25mm ²
Connection cross-sect. rigid cable	1,5 / 35mm ²
European directive WEEE	concerned
Operating temperature	-40...80 °C