



SPB040D

**Cartridge L-N Uc 275V In 20kA I<sub>max</sub> 40kA Up 1,35kV**

**Technical characteristics**

**Controls and indicators**

Indicator lamp	Optic
----------------	-------

**Main electrical features**

Rated operational voltage U <sub>e</sub>	240 / 415 V
Frequency	50/60 Hz

**Dimensions**

Depth of installed product	58.2 mm
Height of installed product	89.8 mm

**Installation, mounting**

Tightening torque	3
-------------------	---

**Use conditions**

Operating temperature	-40...80 °C
-----------------------	-------------