



SPB040N

Cartridge N-PE Uc 260V In 20kA I_{max} 40kA Up 1.5kV

Technical characteristics

Controls and indicators

Indicator lamp	Optic
----------------	-------

Main electrical features

Rated operational voltage U _e	240 / 415 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	58.2 mm
Height of installed product	89.8 mm

Installation, mounting

Tightening torque	3
-------------------	---

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------