



SPB440R

**Surge Protection Device 4P T2 TNS/TT Uc 275V In 20kA I<sub>max</sub> 40kA remote contact**

**Technical characteristics**

**Controls and indicators**

Indicator lamp Optic

**Main electrical features**

Rated operational voltage U<sub>e</sub> 240 / 415 V

**Electric current**

Max discharge (I<sub>max</sub>) L-N(PEN)/ N-PE 40 kA

**Dimensions**

Depth of installed product 58.2 mm

Height of installed product 89.8 mm

Width of installed product 71.2 mm

**Installation, mounting**

Tightening torque 3

**Standards**

European directive WEEE concerned

**Use conditions**

Operating temperature -40...80 °C