



SPB440R

Surge Protection Device 4P T2 TNS/TT Uc 275V In 20kA Imax 40kA remote contact

Technical characteristics

Main electrical features

Rated operational voltage Ue 240 / 415 V

Frequency 50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 40 kA

Dimensions

Depth of installed product 58.2 mm

Height of installed product 89.8 mm

Width of installed product 71.2 mm

Installation, mounting

Tightening torque 3

Standards

European directive WEEE concerned

Use conditions

Operating temperature -40...80 °C