



SPB440R

## Surge Protection Device 4P T2 TNS/TT U<sub>c</sub> 275V I<sub>n</sub> 20kA I<sub>max</sub> 40kA remote contact

### Technical characteristics

#### Controls and indicators

Indicator lamp	Optic
----------------	-------

#### Main electrical features

Rated operational voltage U <sub>e</sub>	240 / 415 V
Frequency	50/60 Hz

#### Electric current

Max discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	40 kA
--	-------

#### Dimensions

Depth of installed product	58.2 mm
Height of installed product	89.8 mm
Width of installed product	71.2 mm

#### Installation, mounting

Tightening torque	3
-------------------	---

#### Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------