



SPB440R

Surge Protection Device 4P T2 TNS/TT Uc 275V In 20kA Imax 40kA remote contact

Technical characteristics

Main electrical features

Rated operational voltage Ue	240 / 415 V
Frequency	50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

Dimensions

Depth of installed product	58.2 mm
Height of installed product	89.8 mm
Width of installed product	71.2 mm

Installation, mounting

Tightening torque	3
-------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------