



SPD215D

SPD 2P pluggable 15kA class 2 with end of life indicator

Technical characteristics

Architecture

Type of pole 1P+N

Controls and indicators

Indicator lamp end of life indicator

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 15 kA

Dimensions

Width of installed product 36 mm

Power

Total power loss under IN 0 W

Installation, mounting

Tightening torque 3,6Nm

Connection

Connection cross-sect. flexible conductor 25mm²

Connection cross-sect. rigid cable 35mm²

Standards

European directive WEEE not concerned

Use conditions

Operating temperature -40...60 °C