



SPD215D

SPD 2P pluggable 15kA class 2 with end of life indicator

Technical characteristics

Architecture

Type of pole	1P+N
--------------	------

Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50/60 Hz

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	15 kA
--	-------

Dimensions

Width of installed product	36 mm
----------------------------	-------

Power

Total power loss under I _N	0 W
---------------------------------------	-----

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	25mm ²
Connection cross-sect. rigid cable	35mm ²

Standards

European directive WEEE	not concerned
-------------------------	---------------

Use conditions

Operating temperature	-40...60 °C
-----------------------	-------------