



SPN015D

## Cartridge 15kA 275V for pluggable SPD

### Technical characteristics

#### Architecture

Number of poles 1 P

#### Controls and indicators

Indicator lamp end of life indicator

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 15 kA

#### Dimensions

Width of installed product 0 mm

#### Power

Total power loss under IN 0 W

#### Use conditions

Operating temperature -40...55 °C