



SPN040D

## Cartridge 40kA 275V for pluggable SPD

### Technical characteristics

#### Architecture

Number of poles 1 P

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Max discharge (I<sub>max</sub>) L-N(PEN)/ N-PE 40 kA

#### Dimensions

Width of installed product 0 mm

#### Power

Total power loss under I<sub>N</sub> 0 W

#### Standards

European directive WEEE concerned

#### Use conditions

Operating temperature -40...55 °C