



SPN040D

Cartridge 40kA 275V for pluggable SPD

Technical characteristics

Architecture

Number of poles 1 P

Controls and indicators

Indicator lamp end of life indicator

Main electrical features

Frequency 50/60 Hz

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 40 kA

Dimensions

Width of installed product 0 mm

Power

Total power loss under IN 0 W

Use conditions

Operating temperature -40...55 °C