



SPN040D

## Cartridge 40kA 275V for pluggable SPD

### Technical characteristics

#### Architecture

Number of poles	1 P
-----------------	-----

#### Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	0 mm
----------------------------	------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------