



SPN040N

Cartridge neutral 40kA 255V for pluggable SPD without reserve

Technical characteristics

Architecture

Number of poles	1 P
-----------------	-----

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	40 kA
--	-------

Dimensions

Width of installed product	0 mm
----------------------------	------

Power

Total power loss under I _N	0 W
---------------------------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------