



SPN040N

Cartridge neutral 40kA 255V for pluggable SPD without reserve

Technical characteristics

Architecture

Number of poles 1 P

Controls and indicators

Indicator lamp no

Main electrical features

Frequency 50/60 Hz

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 40 kA

Dimensions

Width of installed product 0 mm

Power

Total power loss under I_N 0 W

Use conditions

Operating temperature -40...55 °C