



SPN040R

Cartridge 40kA 275V for pluggable SPD with reserve

Technical characteristics

Architecture

Number of poles	1 P
-----------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

Dimensions

Width of installed product	0 mm
----------------------------	------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------