



SPN080

### Cartridge 25kA class 1 for SPN8xxx

#### Technical characteristics

#### Main electrical features

Frequency 50/60 Hz

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 25 kA

#### Power

Total power loss under IN 0 W

#### Standards

European directive WEEE concerned

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -40...60 °C