



SPN080

Cartridge 25kA class 1 for SPN8xxx

Technical characteristics

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE	25 kA
--	-------

Power

Total power loss under I_N	0 W
------------------------------	-----

Use conditions

Operating temperature	-40...60 °C
-----------------------	-------------