



SPN080

### Cartridge 25kA class 1 for SPN8xxx

#### Technical Characteristics

With remote signalling contact	No
Frequency	50/60 Hz
Max discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	25 kA
Total power loss under IN	0 W
Number of modules	1
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-40...60 °C