



SPN115R

SPD 1P pluggable 15kA class 2 with reserve + remote contact

Technical characteristics

Architecture

Type of pole 1 P

Main electrical features

Rated operational voltage U_e 230 / 400 V

Frequency 50/60 Hz

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 15 kA

Power

Total power loss under I_N 0 W

Standards

European directive WEEE concerned

Use conditions

Operating temperature -40...55 °C