



SPN115R

**SPD 1P pluggable 15kA class 2 with reserve + remote contact**

**Technical characteristics**

**Architecture**

Type of pole 1 P

**Controls and indicators**

Indicator lamp reserve

**Main electrical features**

Rated operational voltage  $U_e$  230 / 400 V

Frequency 50/60 Hz

**Electric current**

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE 15 kA

**Power**

Total power loss under IN 0 W

**Installation, mounting**

Tightening torque 3,6Nm

**Connection**

Connection cross-sect. flexible conductor 25mm<sup>2</sup>

Connection cross-sect. rigid cable 35mm<sup>2</sup>

**Use conditions**

Operating temperature -40...55 °C