



SPN140D

## SPD 1P pluggable 40kA class 2 with end of life indicator

### Technical characteristics

#### Architecture

Type of pole	1 P
--------------	-----

#### Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

#### Main electrical features

Rated operational voltage $U_e$	230 V
---------------------------------	-------

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	40 kA
--	-------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	25mm <sup>2</sup>
---	-------------------

Connection cross-sect. rigid cable	35mm <sup>2</sup>
------------------------------------	-------------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------