



SPN208D

## SPD 2P pluggable 8kA class 2 with indicator

### Technical characteristics

#### Controls and indicators

Indicator lamp	reserve
----------------	---------

#### Main electrical features

Rated operational voltage $U_e$	230 V
---------------------------------	-------

#### Electric current

Max discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	8 kA
--	------

#### Dimensions

Width of installed product	35 mm
----------------------------	-------

#### Power

Total power loss under IN	0.1 W
---------------------------	-------

#### Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------